Rittal – The System.

Faster – better – everywhere.



DK 7246.400

Adaptor, 3 U

State: 05/11/2026 (Source: www.rittal.com/com-en)

DK 7246.400 - Adaptor, 3 U Depth offset 100 mm

Used to recess 482.6 mm (19˝) mounting of equipment inside enclosures with 482.6 mm (19˝) installation in the foremost position, such as server or electronic enclosures.



Features

Model No.	DK 7246.400
Product description	This adaptor is used to recess 482.6 mm (19") mounting of equipment inside enclosures with 482.6 mm (19") installation in the foremost position, such as server or electronic enclosures. In this way, sufficient space can be gained in front of the mounting equipment to integrate patch panels or switches, whilst at the same time exploiting the maximum enclosure depth.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Units	3 U
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Packs of	2 pc(s).
Net weight	0.34 kg
Gross weight	0.37 kg
PCF per pack (cradle-to-gate)	1.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

Features

Customs tariff number	83024900
ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	DK Adaptor 482,6 mm (19"), 3 U, Depth offset 100 mm

Tender text

482.6 mm (19") adaptor, 3 U, 100 mm depth offset
Material: Sheet steel, zinc-plated, passivated