Rittal – The System.

Faster – better – everywhere.



DK 7507.740

Levelling feet

State: 05/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7507.740 - Levelling feet for FlatBox, M10 x 20 mm

Levelling feet for FlatBox

Features

Model No.	DK 7507.740
Product description	For screw-fastening into the enclosure base. Width across flats 17, mounting thread multi-tooth 30.
Applications	Instrument case Floor standing enclosures
Function principle	For screw-fastening into the enclosure base
Material	Foot: Plastic
Colour	Foot: RAL 9005
Levelling low	30 mm
Adjustment tool	Hex spanner SW 17
Max. load capacity (static) per component	5,500 N
Dimensions	Thread: M10 Thread length: 20 mm
Levelling range	10 - 20 mm
Packs of	4 pc(s).
Net weight	0.128 kg
Gross weight	0.131 kg
Customs tariff number	39232100
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	DK Levelling feet, For screw-fastening onto the enclosure base, M10x20 mm, For Flatbox,

© Rittal 2026