

Rittal – The System.

Faster – better – everywhere.



DK 7824.188

Side panel, lockable

State: 01/02/2026 (Source: ittal.com/com-en)



DK 7824.188 - Side panel, lockable for TS, TS IT

Side panel, lockable, sheet steel, for TS.



Features

Model No.	DK 7824.188
Product description	Simply locate from above. Lock with security lock no. 3524 E. Earthing bolt with contact track.
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7035
Supply includes	2 side panels each with 4 security locks no. 3524 E
To fit	Enclosure type: TS TS IT Height: 1,800 mm Depth: 800 mm
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	34.4
Gross weight	35.8
Customs tariff number	94039910
EAN	4028177232037
E-Number Sweden	E7282526
ETIM 9	EC002524

Features

ECLASS 8.0

27182101

Tender text

Colour

RAL 7035

Material

Sheet steel, spray-finished

Supply includes

2 side panels with toggle locks

Dimensions mm W x H x D

Height 1800 mm, depth 800 mm