

Rittal – The System.

Faster – better – everywhere.



DK 7824.202 Glazed door, vented

State: 16/05/2025 (Source: [rittal.com/com-en](https://www.rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.202 - Glazed door, vented for TS, TS IT, VX SE

To replace existing doors. With 180° hinges and swivel handle with security lock no. 3524 E.

Features

| | |
|-----------------------|---|
| Model No. | DK 7824.202 |
| Product description | Surface perforated on both sides with air inlet openings > 78% for optimum air throughput. |
| Material | Door: Sheet steel Viewing window: Single-pane safety glass, 3 mm |
| Surface finish | Powder-coated |
| Colour | RAL 7035 |
| Supply includes | Glazed door, vented Comfort handle for profile half-cylinders with security lock 3524 E 180° hinges (4) Assembly parts |
| Assembly instruction | For TS enclosure suites with sheet steel doors, only the 180° hinge 7824.520 may be used. |
| To fit | Enclosure type: TS TS IT SE Width: 800 mm Height: 2,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 24.89 |
| Gross weight | 26.2 |
| Customs tariff number | 94039910 |
| EAN | 4028177236127 |
| ETIM 9 | EC000747 |
| ECLASS 8.0 | 27182204 |

Tender text

Material

Sheet steel, spray-finished

Colour

RAL 7035

Dimensions mm W x H x D

800 x 2000

Lock system

Comfort handle including security insert (no. 3524 E.)