


Rittal – The System.

Faster – better – everywhere.



TS 7826.605

Roof plate for cable entry, two-piece

State: 09/02/2026 (Source: rittal.com/com-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL


IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 7826.605 - Roof plate for cable entry, two-piece for VX, VX IT, TS, TS IT

The two-piece design allows easy retro-fitting, by simply removing the front part of the plate for retrospective cable entry.



Features

| | |
|-----------------------|---|
| Model No. | TS 7826.605 |
| Product description | In exchange for the standard roof. Equipped with a sliding angular bracket in the rear section. Rubber cable clamp strip on both sides for attaching cable bundles and bunched cables. Due to the symmetrical design of the frame, side cable entry can also be achieved by rotating the roof plate. The two-piece design allows convenient retrofitting. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| To fit | Width: 600 mm Depth: 1,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 8.443 |
| Gross weight | 8.887 |
| Customs tariff number | 94039910 |
| EAN | 4028177345355 |
| E-Number Sweden | E7239740 |
| ETIM 9 | EC000744 |

Features

ECLASS 8.0

27182405

Tender text

Cable entry roof plate for TS, TS IT

W x D = 600 x 1000,
two-piece

A cable entry roof plate including assembly parts.

Material: Sheet steel, spray finished in RAL 7035

Dimensions (W x D): 600 mm x 1000 mm