
Rittal – The System.

Faster – better – everywhere.



# TS 7826.665

# Roof plate for cable entry, two-piece


State: 06/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# TS 7826.665 - Roof plate for cable entry, two-piece for VX, VX IT, TS, TS IT

The two-piece design allows easy retro-fitting, by simply removing the front part of the plate for retrospective cable entry.



## Features

| | |
|---|---|
| Model No. | TS 7826.665 |
| Product description | In exchange for the standard roof. Equipped with a sliding angular bracket in the rear section. Rubber cable clamp strip on both sides for attaching cable bundles and bunched cables. Due to the symmetrical design of the frame, side cable entry can also be achieved by rotating the roof plate. The two-piece design allows convenient retrofitting. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| To fit | Width: 600 mm<br>Depth: 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 5.136 kg |
| Gross weight | 5.38 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000744 |
| ECLASS 8.0 | 27182405 |
| Product description | DK-TS8 Roof plate, WxD: 600x600 mm, 2-part, For cable entry |

# Tender text

Roof plate for cable entry, two-piece for TS, TS IT

Material: Sheet steel, spray-finished in RAL 7035
Dimensions (W x D): 600 mm x 600 mm

© Rittal 2026