

# Rittal – The System.

Faster – better – everywhere.



## DK 7828.060 C rails

State: 25/08/2025 (Source: [rittal.com/com-en](http://rittal.com/com-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7828.060 - C rails for TS, VX SE

For direct external mounting between the vertical TS, SE enclosure sections. The C-section angle bracket is additionally required for mounting between the horizontal TS, SE enclosure sections. Thanks to the universal attachment piece, the C rails may be optionally attached to the inner or outer level of the TS 8 frame.

## Features

|                       |   |
|-----------------------|---|
| Model No.             | DK 7828.060   |
| Product description   | For direct external mounting between the vertical TS, SE enclosure sections. The angle bracket, C-section, is additionally required for mounting between the horizontal TS, SE enclosure sections. The universal design of the attachment piece allows the C rails to be optionally attached to the inner or outer level of the TS 8 frame. |
| Material              | Sheet steel   |
| Surface finish        | Zinc-plated   |
| Supply includes       | Assembly parts  |
| Length                | 498 mm  |
| To fit                | Enclosure type: TS<br>SE<br>Width: = 600 mm<br>Depth: = 600 mm  |
| Packs of              | 4 pc(s).  |
| Net weight            | 1.736   |
| Gross weight          | 1.98  |
| Customs tariff number | 73269098  |
| EAN                   | 4028177235052   |
| E-Number Sweden       | E7239810  |
| ETIM 9                | EC000386  |
| ECLASS 8.0            | 27400501  |

# Tender text

C rail for TS 8

Type of attachment: in the enclosure depth

Distance between 19" levels: 445/495 mm

Material: Sheet steel, zinc-plated, passivated

for enclosure dimensions: W: 600 mm D: 600 mm