

Rittal – The System.

Faster – better – everywhere.



DK 7828.102 Cable clamp rail

State: 10/06/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7828.102 - Cable clamp rail for TS, TS IT

The cables may be attached to the cable clamp rails with cable ties or nylon tapes, the cable clamp rails are simply located onto the frame section and may additionally be secured with a screw.

Features

Model No.	DK 7828.102
Design	for the outer attachment level
Product description	For cable routing on the enclosure frame. The cables may be attached to the cable clamp rails with cable ties or nylon loops. The cable clamp rails are easily located onto the frame section of the enclosure frame or mounting frame, and may additionally be secured with a screw.
Applications	On the TS frame between the mounting angles of the TS IT in the enclosure depth
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
To fit	Enclosure type: TS TS IT Width: 1,000 mm Depth: 1,000 mm
Suitable for width	1,000 mm
Packs of	4 pc(s).
Net weight	1.6 kg
Gross weight	1.8 kg
Customs tariff number	73269098
ETIM 9	EC000322
ECLASS 8.0	27400604

Features

Product description

DK Cable clamp rail, For the outer mounting level, For WxD: 1000 mm

Tender text

Cable clamp rail for TS 8 outer mounting level

Material: Sheet steel, zinc-plated, passivated

For enclosure dimensions: W: 1000 mm D: 1000 mm