Rittal – The System.

Faster – better – everywhere.



DK 7856.014

Connection cable

State: 07/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

DK 7856.014 - Connection cable for PSM rail

Connection cable, ready to connect, with adaptor connector C13 (jack) and C14 (connector).

Features

Model No.	DK 7856.014
Product description	Ready-to-use connection cable, with adaptor connector C13 (jack) and C14 (connector).
Connector (type)	IEC 320 connector C14
Rated current (max.)	10 A
Dimensions	Length: 0.5 m
Sockets	IEC 320 socket C13
Packs of	2 pc(s).
Net weight	0.16 kg
Gross weight	0.199 kg
Customs tariff number	85444290
ETIM 9	EC001576
ECLASS 8.0	27060402
Product description	DK Connection cable, L: 0,5 m, 10 A, C13/C14, For PSM

Tender text

Connection cable C13 / C14

0.5 m, completely ready for fitting with transfer plug
from PSM and IEC 320 C14 plug (IEC) 230V / 10A

© Rittal 2026