

Rittal – The System.

Faster – better – everywhere.



DK 7859.090 PSM Zero-U-Space

State: 28/05/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7859.090 - PSM Zero-U-Space

Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.



Features

Model No.	DK 7859.090
Product description	Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.
Material	Aluminium section, natural anodised
Length	1,695 mm
Length of connection cable	3 m
Type of electrical connection	fixed/CEE
Qty.	1
Phases per infeed	1~
Rated current (max.)	32 A
Module slots (max.)	5
IP protection category to IEC 60529	IP 20
Dimensions	Length: 1,695 mm

Features

To fit	Enclosure type: VX IT Height: ≥ 2,000 mm
Operating temperature range	5 °C...45 °C
Ambient humidity (non-condensing)	10...90 %
Packs of	1 pc(s).
Net weight	4.9 kg
Gross weight	5.2 kg
Customs tariff number	85369001
ETIM 9	EC002762
ECLASS 8.0	27371306
Product description	DK modular PDU, PSM busbar, modular power distribution for vertical installation, in the Zero-U-Space for 800 mm wide IT racks, 1~, 32 A, length 1695 mm, module slots: 5, infeeds: 1, connection cable length: 3 m, CEE connector, for enclosure height 2000 mm, aluminium section, natural anodised

Approvals

Explanations	Declaration of conformity
--------------	---------------------------