

Rittal – The System.

Faster – better – everywhere.



DK 7955.134

PDU international, basic version

State: 21/06/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7955.134 - PDU international, basic version

IT rack power distribution in a range of different variants. Input with CEE connector (16 A/32 A) and C13 and C19 outputs. Distribution output from 3.7 kW to 22 kW.

Features

Model No.	DK 7955.134
Design	PDU Basic
Product description	Robust, compact basic power distributor for the IT environment. Thanks to the compact PDU, any IT rack may be easily equipped with a professional power distribution system. With the TS IT rack, assembly is even tool-free. The compact design allows simple assembly.
Material	Aluminium section, black anodised
Dimensions	Width: 44 mm Depth: 62 mm Length: 1,710 mm
No. of sockets and type	36 x C13 / 6 x C19
Sockets	36 x IEC 320 socket C13 6 x IEC 320 socket C19
Rated current (max.)	32 A
Infeeds	Qty.: 1 Phases per infeed: 3~
Length of connection cable	3 m
Type of electrical connection	CEE
Number RJ45 ports for sensor units max	6
Directives	EMC Directive 2014/30/EU Low Voltage Directive 2014/35/EU
Standards	EN 60950-1
Operating temperature range	0 °C...45 °C

Features

Ambient humidity (non-condensing)	10...95 %
Storage temperature range	-25 °C...70 °C
To fit	Enclosure type: TS IT: ≥ 2,000 mm
Packs of	1 pc(s).
ETIM 9	EC002762
ECLASS 8.0	27142604
Product description	DK PDU international, basic version, Compact basic power distributor, WLD: 44x1710x62 mm, 36xC13, 6xC19, black, CEE, 3~, 32 A