Rittal – The System.

Faster – better – everywhere.



# SK 7980.148

# Fan expansion kit

State: 19/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SK 7980.148 - Fan expansion kit

For retrofitting various fan units or to supplement the fan mounting plate

## Features

| | |
|---|---|
| Model No. | SK 7980.148 |
| Product description | For use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate. |
| Supply includes | Fan<br>Connection cable (0.61 m)<br>Assembly parts |
| Air throughput (unimpeded air flow) | 184 m³/h |
| Rated operating voltage | 48 V (DC) |
| Power consumption Pel | With DC: 7.7 W |
| Dimensions | Width: 119 mm<br>Height: 119 mm<br>Depth: 38 mm |
| Operating temperature range | -20 °C...70 °C |
| Noise level | With DC: 43 dB(A) |
| Packs of | 1 pc(s). |
| Net weight | 0.37 kg |
| Gross weight | 0.387 kg |
| Customs tariff number | 84145915 |
| ETIM 9 | EC000320 |
| ECLASS 8.0 | 27180716 |
| Product description | DK Fan expansion kit, for use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate, WxHxD:  119x119x38 mm, 48 V (DC) |

© Rittal 2026

# Tender text

Fan expansion kit, W x H x D = 119 x 119 x 25, 48 V

Air throughput (unimpeded air flow): 184 m³/h
Temperature range: -20°C to +70°C
Dimensions (W x H x D): 119 mm x 119 mm x 25 mm

© Rittal 2026