

Rittal – The System.

Faster – better – everywhere.



DK 7998.606

RiMatrix S

State: 25/06/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7998.606 - RiMatrix S Standard security room

The standardised data centre at your premises is equipped with an additional security room (room-within-a-room) to provide additional protection from fire, water and smoke.

Features

| | |
|---|--|
| Model No. | DK 7998.606 |
| Product description | The standardised data centre at your premises is equipped with an additional security room (room-within-a-room) to provide additional protection from fire, water and smoke. |
| Material | Element core made of thermally effective insulation substance Robust, encapsulated sheet steel cassette panels Innovative connection technology using patented profile technology Use of temperature- and humidity-resistant seals Use of fire protection valves Dismantling and reassembly is possible at any time |
| Supply includes | Advice and ROI calculation Delivery and integration into the customer infrastructure Commissioning and handover Documentation, training and instruction Hotline and service/service agreements |
| Clearance depth | 7,220 mm |
| Clearance height | 2,700 mm |
| Clearance width | 2,750 mm |
| Climate control (ZUCS) | 90 kW + 10 kW n+1 redundant |
| Number of low-voltage main distributors | 1 |
| No. of PDU Basic | 18 |
| Serverracks (600x2000x1200mm) | 8 |
| Combined network/server rack (800 x 2000 x 1200 mm) | 1 |

Features

| | |
|--|--|
| Protection standards | Fire resistance EI 90 to EN 1363/F 90 to DIN 4102 Dust- and watertight IP 56 to IEC 60 529 Protection from unauthorised access – Resistance class II EMC basic protection Acrid gas-tightness, based on EN 1634-3 (DIN 18095) Shock test with 3000 Nm energy after 30 minutes flame impingement over standard temperature curve |
| Burglar resistance | RC 2 |
| Design burglar protection | Yes |
| Design fire protection | EI 90 to EN 1363 / F 90 to DIN 4102 |
| Humidification and dehumidification system | optional |
| Room extinguisher system | optional |
| Version | Single 9 |
| Dimensions | Width: 2,950 mm Height: 2,800 mm Depth: 7,420 mm |
| Packs of | 1 pc(s). |
| Customs tariff number | 73089059 |
| ETIM 9 | EC002499 |
| ECLASS 8.0 | 27180207 |
| Product description | DK RiMatrix S Standard security room, Single 9 |

Tender text

Standard data centre 90 kW, 8+1 racks,
including cooling installed in a security room „

Fully functional standard data centre comprising a
rack suite (depth 1200 mm) with 8 server racks and a
network rack, installed in a fully enclosed housing.

The standard data centre is enclosed in an accurately
dimensioned, modular IT security room. All connecting
elements of the room system are designed to permit
disassembly and re-use. The enclosure is a steel box
construction. The IT security room is installed as a