Rittal – The System.

Faster – better – everywhere.



VX 8108.550

Side panel, screw-fastened, sheet steel

State: 05/11/2026 (Source: www.rittal.com/com-en)

VX 8108.550 - Side panel, screw-fastened, sheet steel C4-H

Side panels, screw-fastened, sheet steel. Surface coating to DIN EN ISO 12944 corrosion protection class C4-H.

Features

Model No.	VX 8108.550
Design	Surface coating to DIN EN ISO 12944 Corrosion protection class C4-H
Material	Sheet steel, 1.5 mm
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Assembly parts
To fit	Enclosure type: VX C4-H Height: = 2,000 mm Depth: = 800 mm
IP protection category to IEC 60 529	IP 55
Type rating to 508A	Type 1 Type 12
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	38 kg
Gross weight	38.32 kg
Customs tariff number	94039910
ETIM 9	EC002524
ETIM 8	EC002524
ECLASS 8.0	27182101

© Rittal 2026

Features

Product description	VX side panel, screw-fastened, for HxD: 2000x800 mm, sheet steel, C4-H