Rittal – The System.

Faster – better – everywhere.



VX 8185.245

Side panel, screw-fastened, sheet steel

State: 18/11/2026 (Source: www.rittal.com/com-en)

VX 8185.245 - Side panel, screw-fastened, sheet steel for VX

Side panels, screw-fastened, sheet steel, for VX.

Features

Model No.	VX 8185.245
Benefits	Time-saving assembly thanks to clip-in side panel holder Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside Easy positioning in the height and depth with the location aid One-person assembly Earthing bolts with large, paint-free contact surface for optimum contact
Material	Sheet steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Colour	RAL 7035
Supply includes	Assembly parts
To fit	Enclosure type: VX Height: = 1,800 mm Depth: = 500 mm
IP protection category to IEC 60 529	IP 55
Type rating to 508A	Type 1 Type 12
Basic material	Sheet steel
Packs of	2 pc(s).
Net weight	21.6 kg
Gross weight	22 kg
PCF per pack (cradle-to-gate)	66.61 kg CO2 eq (Cat B)

© Rittal 2026

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
ETIM 9	EC002524
ECLASS 8.0	27182101
Product description	VX Side panel, screw-fastened, for HD: 1800x500 mm, sheet steel

Approvals

Approvals	UL + C-UL (listed)
Explanations	PCF-declaration