
### Rittal - The System.

Faster – better – everywhere.





### VX 8617.170


# Punched section with mounting flange, 23 x 64 mm

State: 08/12/2025 (Source: rittal.com/com-en)



## VX 8617.170 - Punched section with mounting flange, 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.



#### **Features**

Model No.	VX 8617.170
Product description	For variable, individual interior installation of the enclosure frame or the inner mounting level, and for installation in compact enclosures
Benefits	Simply locate into the system punchings and screw-fasten System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX installation options	In enclosure height 1400 mm, on the inner mounting level
AX installation options	In enclosure height 1400 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
AX stainless steel installation options	In enclosure height 1400 mm, in conjunction with the base configuration rail

© Rittal 2025 2

### **Features**

To fit	Enclosure type: VX VX IT
	AX
	Suitable for width or height or depth: 1,400 mm
Packs of	4 pc(s).
Net weight	5
Gross weight	5.8
Customs tariff number	73269098
EAN	4028177829176
ETIM 9	EC002620
ECLASS 8.0	27189234

© Rittal 2025 3