

Rittal – The System.

Faster – better – everywhere.



VX 8618.000

Glazed door

State: 08/02/2026 (Source: ittal.com/com-en)



FRIEDHELM LOH GROUP

VX 8618.000 - Glazed door for VX

Instead of a sheet steel door or rear panel.

Features

Model No.	VX 8618.000
Product description	Instead of a sheet steel door or rear panel.
Material	Frame: Extruded aluminium section Viewing window: Single-pane safety glass, 3 mm
Surface finish	Powder-coated
Colour	Frame: RAL 7035 Viewing window (printed mask on the inside): RAL 9005
Supply includes	Glazed door Locking rod with double-bit insert 180° hinges (4)
IK Code	IK08
Note	Lock components for frame 8618.110 are required when mounting instead of the rear panel
Type rating to UL 50E	Type 1 Type 12
IP protection category to IEC 60 529	IP 55
To fit	Enclosure type: VX Width: = 600 mm Height: = 1,800 mm
Packs of	1 pc(s).
Net weight	12.4
Gross weight	13
Customs tariff number	94039910
EAN	4028177921085
ETIM 9	EC000747

Features

ECLASS 8.0

27182204

Approvals

Approvals UL + C-UL - FTAA

Certificates Protection category