
### Rittal - The System.

Faster – better – everywhere.





# VX 8620.025

Base/plinth corner piece with base/ plinth trim panels, front and rear, 200 mm

State: 23/10/2025 (Source: rittal.com/com-en)

ENCLOSURES

OWER DISTRIBUTION

LIMATE CONTROL

T INFRASTRUCTURI

SOFTWARE & SERVICES

# VX 8620.025 - Base/plinth corner piece with base/plinth trim panels, front and rear, 200 mm for VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.

#### **Features**

Model No.	VX 8620.025
Product description	Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.
Material	Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic
Colour	RAL 9005
Supply includes	4 base/plinth corner pieces, 200 mm high 4 corner covers 1 baying cover 1 base/plinth trim panel, front/rear, 200 mm high 2 base/plinth trim panels, front/rear, 100 mm high Assembly parts
Note	Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth
Dimensions	Height: 200 mm
To fit	Enclosure type: VX Width: = 1,200 mm
Weight/pack	11 kg

© Rittal 2025

2

## Features

Packs of	2 pc(s).
Net weight	10.8
Gross weight	10.97
Customs tariff number	94039910
EAN	4028177922143
E-Number Sweden	E3465058
ECLASS 8.0	27182003

## **Approvals**

Approvals UL + C-UL - FTTA

© Rittal 2025 3