


Rittal – The System.

Faster – better – everywhere.



TS 8700.840

Side panels, screw-fastened, stainless steel

State: 11/07/2025 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8700.840 - Side panels, screw-fastened, stainless steel for TS

Side panels, screw-fastened, stainless steel, for TS.



Features

| | |
|-------------------------------------|--|
| Model No. | TS 8700.840 |
| Benefits | Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface |
| Material | Stainless steel 1.4301 (AISI 304), 1.5 mm |
| Surface finish | Brushed, grain 400 |
| Supply includes | Assembly parts |
| To fit | Enclosure type: TS Height: = 1,800 mm Depth: = 400 mm |
| IP protection category to IEC 60529 | IP 55 |
| Basic material | Stainless steel |

Features

| | |
|--------------|---------------|
| Packs of | 2 pc(s). |
| Net weight | 18 |
| Gross weight | 18.4 |
| EAN | 4028177300101 |
| ETIM 9 | EC002524 |
| ECLASS 8.0 | 27182101 |

Tender text

Side panel, screw-fastened, stainless steel TS
Screw-fastened side panel, easy positioning on the frame with the location aid.
Automatic potential equalisation and higher EMC protection thanks to enclosure panel fasteners with contact elements.
Protection category IP 55 to IEC 60529
Hinged version (optional), max. opening angle 180°.
Material: Stainless steel 1.4301 (AISI 304), 1.5 mm
Surface finish: Brushed, grain 400
for enclosure dimensions: H: 1800 mm D: 400 mm
Side panel, screw-fastened, stainless steel 8700.840