

# Rittal – The System.

Faster – better – everywhere.



TS 8801.570

Partial doors

State: 12/06/2026 (Source: rittal.com/com-en)



FRIEDHELM LOH GROUP



# TS 8801.570 - Partial doors for TS

Door may be optionally hinged on the right or left.



## Features

Model No.	TS 8801.570
Design	With 3 mm single-pane safety glass
Product description	Suitable for TS enclosures instead of a door or rear panel. The partial doors may be combined with one another as required. A trim panel is required at the top and bottom in each case. Door may be optionally hinged on the right or left. In the case of doors without viewing panel (height 600 – 1000 mm), monitor frame SZ 2305.000 may be installed. Standard double-bit lock insert may be exchanged for lock inserts, type F, and from 600 mm height, for comfort handle.
Material	Sheet steel, 2 mm
Colour	RAL 7035
Supply includes	Cross member Hinges Lock components Assembly parts
Dimensions	Width: 600 mm Height: 600 mm

# Features

---

IP protection category to IEC 60529	IP 54 for a completed enclosure
-------------------------------------	---------------------------------

---

Packs of	1 pc(s).
----------	----------

---

Net weight	6.08 kg
------------	---------

---

Gross weight	6.4 kg
--------------	--------

---

Customs tariff number	94039910
-----------------------	----------

---

ETIM 9	EC000747
--------	----------

---

ECLASS 8.0	27182204
------------	----------

---