

Rittal – The System.

Faster – better – everywhere.



RX 9364.004 RiLineX fuse holder

State: 03/04/2026 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9364.004 - RiLineX fuse holder

Compact RiLineX class CC fuse holder for 60 mm busbar systems. For class CC cylindrical fuse (30 A) with optical LED fuse monitoring. For reliable contact of cylindrical fuses, the device has special fuse holders that are lockable in the open state and sealable in the closed state. Spring terminal blocks up to 6 mm² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm. Includes electronic fuse monitoring.



Features

Model No.	RX 9364.004
Benefits	Snap-on mounting and simple adjustment for busbar thickness (5/10 mm) with electronic fuse monitoring
Material	Polyamide (PA 6) Fire protection corresponding to UL 94-V0
General colour	RAL 9005 RAL 35745
Rated current (max.)	30 A
Type of electrical connection	Spring terminal
Rated operating voltage	600 V AC
Number of poles	3-pole

Features

Dimensions	Width: 27 mm Height: 263 mm Depth: 123.5 mm
Connection of round conductors, fine wire with wire end ferrule	1.5 - 6 mm ²
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Fuse inserts	Class CC
For fuse type (class)	Fuse Class CC
Packs of	4 pc(s).
Customs tariff number	85369095

Tender text

RiLineX Bus-mounting fuse base (Typ Fuseholder with EFM)

Bus-mounting fuse base for
class CC cylindrical fuse.

Fuses insters are operated individually or
collectively via a front slide.

Optical fuse monitoring with LED.

Conductor connection via tension spring terminals.

Rated voltage 600 V AC.

With UL approval

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 30 A

Connection: 1,5 - 6 mm²

Cable outlet: bottom

Feature: Electronic fuse monitoring

Dimensions: 27 mm x 263 mm x 95 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9364004