

Rittal – The System.

Faster – better – everywhere.



SV 9613.000

**Mini-PLS busbar connection
adaptor**

State: 23/09/2024 (Source: rittal.com/com-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9613.000 - Mini-PLS busbar connection adaptor

Rated current 63 A/1600 A/250 A, cable outlet top/bottom

Features

Model No.	SV 9613.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035 Chassis: RAL 9011
Clamping area for laminated copper bars (W x H)	10 x 8 mm
Note	Wire end ferrules should be used with fine wire conductors
Cable outlet	Top/bottom
Rated operating voltage	690 V
Rated current max.	63 A
Dimensions	Width: 54 mm Height: 160 mm
Connection for round conductor cross-sections	1.5 - 35 mm ²
Packs of	1 pc(s).
Weight/pack	0.45 kg
Net weight	0.3
Gross weight	0.38
Copper weight (kg per piece)	0.081
Customs tariff number	85369010
EAN	4028177140738
ETIM 7.0	EC001531
ECLASS 8.0	27370304

Approvals

Approvals

UR + C-UR (recognized)

Explanations

Declaration of conformity

Declaration of conformity UK