Rittal – The System.

Faster – better – everywhere.



SV 9630.005

Mini-PLS bus-mounting fuse bases

State: 05/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SV 9630.005 - Mini-PLS bus-mounting fuse bases

Rated current 63 A





Features

Model No.	SV 9630.005
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	Chassis: RAL 9011 Cover: RAL 7035
Type of electrical connection	Spring terminal
Fuse inserts	D 02-E 18
Rated current max.	63 A
Dimensions	Width: 39.5 mm Height: 189 mm
Connection of round conductors	1.5 - 16 mm²
Packs of	1 pc(s).
Net weight	0.34 kg
Gross weight	0.374 kg
Copper weight (kg per piece)	0.11
Customs tariff number	85369095
ETIM 9	EC001644

© Rittal 2026

Features

ECLASS 8.0	27142120
Product description	SV Mini-PLS bus-mounting fuse base, D02-E18, 63 A, 400 V, 3-pole, round conductor connection 1,5-16 mm², tension spring clamp, WH: 39,5x189 mm

Approvals

Explanations	Declaration of conformity