Rittal – The System.

Faster – better – everywhere.



# SV 9677.770
# Component adaptor

State: 07/11/2026 (Source: www.rittal.com/com-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# SV 9677.770 - Component adaptor clamping attachment

For circuit-breakers from ABB, Eaton, Schneider Electric and Siemens. For bar systems with 185 mm centre-to-centre spacing.

## Features

| | |
|---|---|
| Model No. | SV 9677.770 |
| Material | Polyamide<br>Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| Supply includes | Connection straps |
| For bar systems with centre-to-centre spacing | 185 mm |
| Cable outlet | Bottom |
| Installation type | Clamping attachment |
| Number of poles | 3-pole |
| Rated current max. | 630 A |
| Rated operating voltage | 690 V, 3~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear<br>Suitable for the use of switchgear with front screw terminal<br>For mounting on busbar systems with or without cover section |
| Dimensions | Width: 150 mm<br>Height: 585 mm |
| To fit busbars | Height: 10 mm |
| To fit manufacturer (model) | ABB (Tmax T5)<br>Eaton (NZM3)<br>Schneider Electric (NSX630)<br>Siemens (3VA23, 3VA24, 3VL4) |
| Packs of | 1 pc(s). |
| Net weight | 6.2 kg |

© Rittal 2026

# Features

| | |
|---|---|
| Gross weight | 6.629 kg |
| Copper weight (kg per piece) | 3.754 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Component adaptor, 630 A, 690 V, 3-pole, 185 mm, clamping attachment |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |