Rittal – The System.

Faster – better – everywhere.





CS 9783.520 Outdoor Basic enclosures

State: 04/11/2025 (Source: rittal.com/com-en)



CS 9783.520 - Outdoor Basic enclosures

Single-walled enclosure systems, one-door and two-door. Ready to use in all applications with passive interior installation or minimal heat loss in the outdoor sector. Roof concept with all-round louvred grilles







Features

Model No.	CS 9783.520
Product description	Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides.
Material	Aluminium AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Colour	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and profile half- cylinder, lock BJ 20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy
Dimensions	Width: 800 mm Height: 1,200 mm Depth: 400 mm

© Rittal 2025 2

Features

Overall height: 1,355 mm	
Rain canopy width: 850 mm	
Rain canopy height: 55 mm	
Rain canopy depth: 450 mm	
Clearance width: 712 mm Clearance height: 1,112 mm Clearance depth: 349 mm	
	Height base/plinth: 100 mm
	Type 3R
IP 55	
IK10	
Aluminium	
1 pc(s).	
46	
48	
4028177569126	
EC000261	
27180101	

© Rittal 2025 3