

Rittal – The System.

Faster – better – everywhere.



SZ 1.895.2500.50

V-INOX-Ex-d

Estado: 18/03/2026 (Fuente: rittal.com/es-es)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1.895.2500.50 - V-INOX-Ex-d

Tapones roscados de acero inoxidable para lugares peligrosos

Características

Referencia	SZ 1.895.2500.50
Descripción producto	Tapones roscados de acero inoxidable para lugares peligrosos
Material	Acero inoxidable 1.4404 (AISI 316L) O-Ring: NBR
Tipo de rosca	métrico
Rosca exterior métrica	M50 x 1,5
Campo de temperatura de servicio	-20 °C...95 °C
Unidad de embalaje	5 pza(s).
Código arancelario	74122000
ECLASS 8.0	27149112
Descripción producto	V-INOX-Ex-d M25 / -20°C - 95°C