

Rittal – The System.

Faster – better – everywhere.



BG 1577.450

Bus enclosures BG

State: 17/07/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



BG 1577.450 - Bus enclosures BG

Wall-mounted enclosure with door of sheet steel, with polycarbonate viewing window. Protection category IP 65. Bus modules of virtually all makes may be attached.

Features

| | |
|-----------------------------------|--|
| Model No. | BG 1577.450 |
| Material | Enclosure: Sheet steel Door: Sheet steel Viewing window: Polycarbonate, 4 mm |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure with door Viewing window in the door Mounting plate |
| Protection category NEMA | NEMA 12 |
| Protection category to IEC 60 529 | IP 65 |
| IK Code | IK08 |
| Dimensions | Width: 400 mm Height: 300 mm Depth: 155 mm |
| Dimensions mounting plate (W x H) | 385 mm x 275 mm |
| Visible area | Viewing window width: 340 mm Viewing window height: 155 mm Distance bottom edge of window - bottom edge of door: 92 mm |
| Material thickness - enclosure | 1.38 mm |
| Material thickness - door | 1.25 mm |
| Door hinge position | bottom |

Features

| | |
|-----------------------|---|
| Lock | Lock version: Cam Number of locks: 1 Lock insert: 3 mm double-bit |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 6.6 |
| Gross weight | 6.8 |
| Customs tariff number | 94032080 |
| EAN | 4028177460058 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Approvals | Lloyds Register of Shipping UL + C-UL (listed) |
| Explanations | Declaration of conformity |