Rittal – The System.

Faster – better – everywhere.






AX 2363.010 Protective roof


State: 09/12/2025 (Source: rittal.com/gr-en)



AX 2363.010 - Protective roof for AX

The sloping protective roof reliably protects the enclosure from standing moisture and other soiling from above.







Features

Model No.	AX 2363.010
Product description	The sloping protective roof reliably protects the enclosure from standing moisture and other soiling from above.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 240
Supply includes	Assembly parts
Installation options	May also be screw-fastened for dynamic loads
Dimensions	Height: 43 mm
Type rating to UL 50E	Type 1
	Type 3R
	Type 4
	Type 4X
	Type 12
To fit	Enclosure type: AX
	Width: = 1,000 mm
	Depth: = 300 mm
Packs of	1 pc(s).
Net weight	4.4

© Rittal 2025

Features

Gross weight	4.7
Customs tariff number	94039910
EAN	4028177938137
E-Number Sweden	E3465323
ETIM 9	EC000744
ETIM 8	EC000744
ECLASS 8.0	27182405

Approvals

Approvals UL + C-UL - FTTA