


Rittal – The System.

Faster – better – everywhere.



SG 2372.031

LED steady light component

State: 16/01/2026 (Source: rittal.com/gr-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SG 2372.031 - LED steady light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system.

Features

| | |
|-----------------------------------|---|
| Model No. | SG 2372.031 |
| Design | LED steady light component |
| Benefits | With 360° signal transmission thanks to optimised prism system Configuration of up to five components with the same voltage. |
| Function principle | A modular layout is possible with connection, optical and acoustic components and a label panel |
| Material | Enclosure of polyamide Cap: Transparent polycarbonate |
| Colour | Clear |
| Protection category to IEC 60 529 | IP 65 if a cover or acoustic component is fitted at the top |
| Rated operating voltage | 24 V (AC/DC) |
| Packs of | 1 pc(s). |
| Net weight | 0.07 |
| Gross weight | 0.073 |
| Customs tariff number | 85311095 |
| EAN | 4028177953741 |
| ETIM 9 | EC000232 |
| ETIM 8 | EC000232 |
| ECLASS 8.0 | 27371220 |

Approvals

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
