

**Rittal – The System.**

Faster – better – everywhere.



# SG 2374.060

## Incandescent lamps

State: 24/06/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2374.060 - Incandescent lamps for steady light components

With BA 15d base.

## Features

|   |   |
|---|---|
| Model No.                                       | SG 2374.060   |
| Product description                             | With BA 15d base.   |
| Benefits  | Simple assembly and contact via bayonet fastener.   |
| Function principle                              | A modular layout is possible with connection, optical and acoustic components, incandescent lamps and a label panel |
| Power consumption (approx.)                     | 5 W   |
| Rated impulse withstand voltage, phase to phase | 28 V AC   |
| Rated insulation voltage                        | 2000 V AC   |
| Rated operating voltage                         | 24 V  |
| Packs of  | 3 pc(s).  |
| Net weight                                      | 0.024   |
| Gross weight                                    | 0.026   |
| Customs tariff number                           | 85392198  |
| EAN   | 4028177219885   |
| ETIM 9  | EC000232  |
| ETIM 8  | EC000232  |
| ECLASS 8.0                                      | 27371220  |