


Rittal – The System.

Faster – better – everywhere.



SZ 2422.000

Spacer

State: 22/05/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2422.000 - Spacer for roof plate

To raise the roof for ventilation purposes, in three different heights. Not suitable for crane transportation.



Features

| | |
|-------------------------------|--|
| Model No. | SZ 2422.000 |
| Product description | To raise the roof for ventilation purposes, in three different heights. |
| Material | Hexagon steel section |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Assembly instruction | Not suitable for crane transportation |
| Dimensions | Height: 10 mm |
| Dimensions | Thread: M12 |
| To fit | Enclosure type: VX TS |
| Packs of | 4 pc(s). |
| Net weight | 0.12 kg |
| Gross weight | 0.161 kg |
| PCF per pack (cradle-to-gate) | 0.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |

Features

| | |
|---------------------|--|
| ETIM 9 | EC002625 |
| ETIM 8 | EC002625 |
| ECLASS 8.0 | 27189234 |
| Product description | SZ Spacer, for TS roof plate, H: 10 mm |
