Rittal – The System.

Faster – better – everywhere.





SZ 2423.000 Spacer

State: 14/12/2025 (Source: rittal.com/gr-en)



SZ 2423.000 - Spacer for roof plate

To raise the roof for ventilation purposes, in three different heights. Not suitable for crane transportation.



Features

Model No.	SZ 2423.000
Product description	To raise the roof for ventilation purposes, in three different heights.
Material	Hexagon steel section
Surface finish	Zinc-plated
Supply includes	Assembly parts
Assembly instruction	Not suitable for crane transportation
Dimensions	Height: 20 mm
Dimensions	Thread: M12
To fit	Enclosure type: VX TS
Packs of	4 pc(s).
Net weight	0.216
Gross weight	0.255
PCF per pack (cradle-to-gate)	1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098

© Rittal 2025 2

Features

EAN	4028177022799
E-Number Sweden	E7239675
ETIM 9	EC002625
ETIM 8	EC002625
ECLASS 8.0	27189234

© Rittal 2025 3