



Rittal – The System.

Faster – better – everywhere.



SZ 2500.114 LED system light

State: 03/09/2025 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2500.114 - LED system light

LED system light – the first light especially for enclosures! Highly innovative LED technology for even more light into the very last corner.



Features

| | |
|--------------------|--|
| Model No. | SZ 2500.114 |
| Design | Without socket |
| Benefits | Optimum illumination of the entire enclosure Optionally with clip, screw and magnetic attachment A configuration to suit every application |
| Design | Without socket |
| Material | Light body: Extruded aluminium Light cover: Polycarbonate Light ends: PC-ABS |
| Colour | Enclosure: RAL 7016 |
| Supply includes | Assembly screws |
| Power consumption | 7 W |
| Connection options | Infeed, 2-pole Through-wiring, 2-pole Door-operated switch |
| Protection class | II (all-insulated) |

Features

| | |
|-------------------------------------|---|
| Light – installation type | Screw-fastening Clip attachment Magnetic attachment (accessory) |
| Installation options | The internal mounting rail AX and the mounting bracket are required when installing in compact enclosures Directly onto the enclosure section with 25 mm pitch pattern |
| Luminous flux | 600 lm |
| Light colour | 4000 K (neutral white) |
| Note | Connection accessories should be ordered separately |
| Dimensions | Width: 337 mm Height: 55 mm Depth: 23 mm |
| Operating temperature range | -20 °C...55 °C |
| Rated operating voltage | 100 V - 230 V, 1~, 50 Hz/60 Hz |
| IP protection category to IEC 60529 | IP 20 |
| Packs of | 1 pc(s). |
| Net weight | 0.36 |
| Gross weight | 0.362 |
| Customs tariff number | 94054990 |
| EAN | 4028177920545 |
| E-Number Sweden | E3465305 |
| ETIM 9 | EC000321 |
| ETIM 8 | EC000321 |
| ECLASS 8.0 | 27189241 |

Approvals

| | |
|-----------|----|
| Approvals | UL |
|-----------|----|

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK