

Rittal – The System.

Faster – better – everywhere.



SZ 2563.100

Metal gland plate

State: 30/01/2026 (Source: [ittal.com/gr-en](https://www.ittal.com/gr-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 2563.100 - Metal gland plate with metric knockouts

Simply knock out the holes for the cable glands using a screwdriver, IP 66 when mounting in the usual position at the bottom.

Features

| | |
|-----------------------------------|---|
| Model No. | SZ 2563.100 |
| Product description | Simply knock out the holes for the cable glands using a screwdriver. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Note | The allocation of gland plate sizes is indicated on the relevant enclosures |
| No. of metric knockouts | 1 x M12 12 x M20 11 x M25 8 x M32 4 x M40 |
| Dimensions | Width: 534 mm Depth: 149 mm |
| To fit | Enclosure type: AE |
| Gland plate | Size: 5 |
| Protection category to IEC 60 529 | IP 66 when mounting in the usual position at the bottom |
| Number knockouts | 1 12 11 8 4 |
| Metric diameter | M12 M20 M25 M32 M40 |
| Packs of | 1 pc(s). |

Features

| | |
|-----------------------|---------------|
| Net weight | 0.96 |
| Gross weight | 1.004 |
| Customs tariff number | 73079100 |
| EAN | 4028177390874 |
| E-Number Sweden | E3404797 |
| ETIM 9 | EC000211 |
| ETIM 8 | EC000211 |
| ECLASS 8.0 | 27142421 |