

Rittal – The System.

Faster – better – everywhere.



FT 2760.010 Viewing window

State: 11/01/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



FT 2760.010 - Viewing window for AX

For external mounting on AX enclosures instead of a door and on surfaces.



Features

Model No.	FT 2760.010
Design	60 section
Product description	For external mounting on AX enclosures instead of a door and on surfaces.
Material	Frame: Aluminium, natural anodised. Glass panel: Acrylic
Supply includes	Plastic handle with lock insert no. 3524 E
Protection category to IEC 60 529	IP 54
To fit Model No.	1039.000 1339.000 1009.000
To fit	Enclosure type: AX Width: = 600 mm Height: = 380 mm
Dimensions	Width: 597 mm Height: 377 mm Depth: 62 mm
Visible area	Viewing window width: 537 mm Viewing window height: 317 mm

Features

Build depth for components (max.)	58 mm
-----------------------------------	-------

Packs of	1 pc(s).
----------	----------

Net weight	3.245
------------	-------

Gross weight	3.3
--------------	-----

Customs tariff number	76101000
-----------------------	----------

EAN	4028177938571
-----	---------------

ETIM 9	EC002527
--------	----------

ETIM 8	EC002527
--------	----------

ECLASS 8.0	27182204
------------	----------
