Rittal – The System.

Faster - better - everywhere.





FT 2784.000 Acrylic glazed cover

State: 07/12/2025 (Source: rittal.com/gr-en)



FT 2784.000 - Acrylic glazed cover

For the protection of display and control components in standard 482.6 mm (19") or metric sizes.

Features

Model No.	FT 2784.000
Design	Metric
Product description	With security lock, lock no. 3524 E.
Material	Frame: Extruded aluminium sections with die-cast corner pieces Glass panel: Smoked acrylic
Supply includes	Hinges and assembly parts. Lock insert no. 3524 E
Protection category to IEC 60 529	IP 54
Dimensions	Width: 400 mm Height: 200 mm Depth: 47.5 mm
Visible area	Viewing window width: 360 mm Viewing window height: 179.5 mm
Build depth for components (max.)	43 mm
Packs of	1 pc(s).
Net weight	1.3
Gross weight	1.4
Customs tariff number	39205100
EAN	4028177032279
ETIM 9	EC002527
ETIM 8	EC002527
ECLASS 8.0	27182301

© Rittal 2025