Rittal - The System.

Faster – better – everywhere.





AX 2820.122

Base/plinth corner piece with base/ plinth trim panels, front and rear, 200 mm

State: 23/10/2025 (Source: rittal.com/gr-en)

ICLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

INFRASTRUCTUR

SOFTWARE & SERVICE

AX 2820.122 - Base/plinth corner piece with base/plinth trim panels, front and rear, 200 mm for AX

Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.

Features

Model No.	AX 2820.122
Product description	Base/plinth corner piece with large opening for optimum access to the screw-fastening point, may be concealed with a plastic corner cover.
Material	Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner cover: Plastic
Colour	RAL 9005
Supply includes	4 base/plinth corner pieces, 200 mm high 4 corner covers 1 base/plinth trim panel, front/rear, 200 mm high 2 base/plinth trim panels, front/rear, 100 mm high Assembly parts
Note	Base/plinth elements are required at the side to finish off a base/ plinth unit Components from the 1st generation base/plinth system cannot be combined with components from the 2nd generation base/plinth system
Dimensions	Height: 200 mm
To fit	Enclosure type: AX Width: = 1,200 mm
Type rating to UL 50E	Type 1 Type 3R Type 4 Type 12
Packs of	2 pc(s).

© Rittal 2025

Features

Net weight	11.5
Gross weight	11.58
Customs tariff number	94039910
EAN	4028177942622
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025 3