Rittal – The System.

Faster – better – everywhere.






SV 3073.000 Busbar support

State: 10/11/2025 (Source: rittal.com/gr-en)



SV 3073.000 - Busbar support

For busbar systems 1250 A (100 mm), 1600 A (185 mm), 2500 A (150 mm), 3000 A (150 mm).



Features

Model No.	SV 3073.000
Material	Fibreglass-reinforced, thermoplastic polyester (PBT) Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Number of poles	3-pole
	100 mm
To fit busbars	30 x 10
	40 x 10
	50 x 10
	60 x 10
Rated current max.	1,250 A
Dimensions	Width: 22 mm
	Height: 320 mm
	Depth: 70 mm
Packs of	4 pc(s).
Net weight	1.612
Gross weight	1.83
Customs tariff number	85469010
EAN	4028177036079
ETIM 9	EC001166

© Rittal 2025

Features

ETIM 8	EC001166
ECLASS 8.0	27400607

Approvals

Explanations Declaration of conformity

Declaration of conformity UK

Tender text

SV busbar support

for accommodating busbars. 3-pole busbar support

with 100 mm bar centre distance.

Rated operating voltage: 1000 V~, 50/60 Hz

to VDE 0660

Rated current: up to 1250 A

Material: PBT

Fire protection: UL 94-V0

Continuous operating temperature: 140 °C

Bar centre distance: 100 mm

Bar accommodation without inserts: 60 x 10 mm

Tightening torques

Assembly screws: 8 - 10 Nm Lid attachment: 1 - 3 Nm

Approvals:

DNV, GL, VDE, ÖVE, SEV, KEMA

© Rittal 2025