


# Rittal – The System.

Faster – better – everywhere.



## SK 3164.610

### Roof-mounted fans

State: 04/03/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3164.610 - Roof-mounted fans for VX, VX IT

Roof-mounted fan for the office sector with exceptionally low noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m<sup>3</sup>/h).

## Features

|                                     |                                                                                                                                      |
|-------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                           | SK 3164.610                                                                                                                          |
| Benefits                            | Easy assembly, the roof plate variant eliminates the need to create mounting cut-outs<br>Fully wired ready for connection            |
| Material                            | Sheet steel, spray-finished                                                                                                          |
| Colour                              | RAL 7035                                                                                                                             |
| Supply includes                     | Roof-mounted fans<br>Assembly parts                                                                                                  |
| Rated operating voltage             | 115 V (DC), 1~, 50 Hz/60 Hz<br>110 V (DC)                                                                                            |
| Rated current max.                  | At 50 Hz: 0.6 A<br>At 60 Hz: 0.7 A                                                                                                   |
| Dimensions                          | Width: 800 mm<br>Height: 240 mm<br>Depth: 800 mm                                                                                     |
| IP protection category to IEC 60529 | Internal circuit IP 54                                                                                                               |
| Note                                | Reduction in the specified air throughput to 800 m <sup>3</sup> /h at 40 Pa counterpressure using two vented base/plinth trim panels |
| Operating temperature range         | 20 °C...55 °C                                                                                                                        |
| Packs of                            | 1 pc(s).                                                                                                                             |
| Net weight                          | 31.35 kg                                                                                                                             |
| Gross weight                        | 33 kg                                                                                                                                |
| Customs tariff number               | 84145915                                                                                                                             |
| ECLASS 8.0                          | 27180716                                                                                                                             |

# Approvals

|              |                                                           |
|--------------|-----------------------------------------------------------|
| Certificates | EAC                                                       |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

## Tender text

SK roof-mounted fan for TS 8

Roof-mounted fan fitted onto a roof plate based on TS 8 with cable entry.

Easy assembly, and the need to create mounting cutouts has been eliminated.

Retrofitting possible.

High volumetric air flow (unimpeded air flow), 1500m<sup>3</sup>/h at a low noise level of 40 dB (A).

Fully wired ready for connection.

Dimensions mm (WxHxD) incl. roof plate: 800x240x800

Rated operating voltage V,Hz: 115,50/60

Temperature range: +20°C to +50°

Surface finish: RAL 7035