

# Rittal – The System.

Faster – better – everywhere.



## SK 3314.030

## Touchscreen display, colour

State: 24/08/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3314.030 - Touchscreen display, colour for LCP Rack/ Inline CW

All relevant operating parameters are displayed directly on the LCP display, to allow directly monitoring of key LCP functions and the implementation of settings.



## Features

Model No.	SK 3314.030
Product description	The display offers the opportunity of directly monitoring key functions of the LCP, and implementing settings.
Material	Plastic
Colour	RAL 9005
Supply includes	Touchscreen display, colour Assembly parts
To fit Model No.	SK 3314.130/230/238/250/260/268/530/538/540/542/548/550/560/568/570 SK 3314.020/025
Packs of	1 pc(s).
Net weight	0.27
Gross weight	0.307
Customs tariff number	85312040
EAN	4028177984950
ECLASS 8.0	27180712

# Tender text

Tender text Touch-Screen Display, SK3314.030

for LCP Rack / Inline CW

SK3314.130/230/238/250/260/268/530/538/540/542/548/560/568/570 and  
LCP Rear Door CW active modules SK3314.020/025

Touch screen display, colour, SK3314.030

The display shows the user all relevant operating parameters directly on the LCP.

This has the advantage that the status of the device can be recognised quickly and at a glance, if necessary, the user can react and change parameters as quickly as possible.

The following parameters can be read and changed at various levels:

- Display of the cold air temperature supplied to the 19' equipment
- Display of the hot air temperature discharged from the 19' equipment
- Display of control mode (automatic, manual, remote)
- Configuration menu: Air Circuit, Coolant circuit, Condensate management, Fan Registry
- Cooling water flow temperature / return temperature
- Cooling water flow rate
- Position of the control valve
- Display of pPUE, EER and Cap (cooling capacity)
- Overview of all parameters and the option to change them (PIN-protected)
- Display of alarm and warning messages
- Overview page with IP address of the device, software version and contact person etc. (can be entered individually)

Touch screen display, packaging unit consisting of:

- Colour touch-screen display, incl. mounting accessories
- 4.3' display, 480 x 272 pixels
- Resistive touch
- Brightness 200 cd/m<sup>2</sup>
- Storage temperature: -20°C to +70°C
- Earthing cable