
Rittal – The System.

Faster - better - everywhere.





SV 3455.500 Conductor connection clamp

State: 04/11/2025 (Source: rittal.com/gr-en)



SV 3455.500 - Conductor connection clamp

For connecting round conductors and laminated copper bars.

Features

SV 3455.500
For connecting round conductors and laminated copper bars.
Sheet steel
Zinc-plated, passivated
Wire end ferrules should be used with fine wire conductors
1 - 4 mm²
10 mm
15 pc(s).
0.285
0.303
1.1 kg CO2 eq (Cat B)
Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
85369010
4028177042735
EC000001
EC000001
27141146

Approvals

© Rittal 2025

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK

Tender text

SV conductor connection clamps

for E-CU busbars and Rittal PLS.

For bar thickness: 10 mm

Connection of round conductors: 1 - 4 mm2

Wire end ferrules should be used with

fine wire conductors

Tightening torque

Conductor connection clamp: 2 Nm

Material: sheet steel, zinc plated, passivated

© Rittal 2025 3