


# Rittal – The System.

Faster – better – everywhere.



## HD 4000.082 Viewing window HD

State: 11/07/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.082 - Viewing window HD

For the protection of switches or displays.

## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | HD 4000.082   |
| Product description                 | For the protection of switches or displays.   |
| Benefits                            | Large viewing panel<br>Gap-free transition between the viewing window and the frame<br>External hinge<br>With T handle for easy opening without a key |
| Material                            | Frame: Stainless steel 1.4301 (AISI 304)<br>Seal: Silicone, compliant with FDA Guideline 21 CFR 177.2600<br>Viewing window: Polycarbonate             |
| Supply includes                     | 2 hinges<br>T handle<br>Assembly parts  |
| Visible area                        | Viewing window width: 352 mm<br>Viewing window height: 185 mm   |
| Dimensions                          | Width: 470 mm<br>Height: 290 mm<br>Depth: 65 mm   |
| To fit                              | Enclosure type: HD compact enclosure  |
| IP protection category to IEC 60529 | IP 55   |
| IK Code                             | IK08  |
| Installation options                | For external mounting on surfaces.  |
| Type rating to UL 50E               | Type 1<br>Type 12<br>Type 13  |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 2.84 kg   |

# Features

---

|                       |  |
|-----------------------|--|
| Gross weight          | 2.896 kg   |
| Customs tariff number | 39252000   |
| ETIM 9                | EC002527   |
| ETIM 8                | EC002527   |
| ECLASS 8.0            | 27182204   |
| Product description   | HD viewing window, with T handle, WxH: 470x290 mm, stainless steel, 1.4301 |

---