



HD 4000.240 - Levelling feet HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

Features

| | |
|-----------------------|--|
| Model No. | HD 4000.240 |
| Design | without base mount |
| Benefits | Minimises cleaning time thanks to fully covered, permanently sealed threads Compensation of floor inclines up to an angle of 10° thanks to flexible base Baying can even be achieved on sloping floors, thanks to a large levelling range Certification to 3-A Sanitary Standards |
| Material | Stainless steel 1.4301 (AISI 304) |
| Supply includes | Assembly parts and seals |
| Load capacity | Max. 7000 N static per levelling foot |
| Dimensions | Thread: M12 |
| To fit | Enclosure type: HD compact enclosure VX VX SE TS |
| Levelling range | 122 - 175 mm |
| Packs of | 4 pc(s). |
| Net weight | 2 kg |
| Gross weight | 2.342 kg |
| Customs tariff number | 73181900 |
| ETIM 9 | EC002622 |
| ETIM 8 | EC002622 |
| ECLASS 8.0 | 27189263 |

Features

Product description

HD Levelling foot, without base mount, Stainless steel 1.4301