

# Rittal – The System.

Faster – better – everywhere.



## HD 4000.240 Levelling feet HD

State: 08/07/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.240 - Levelling feet HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

## Features

Model No.	HD 4000.240
Design	without base mount
Benefits	Minimises cleaning time thanks to fully covered, permanently sealed threads Compensation of floor inclines up to an angle of 10° thanks to flexible base Baying can even be achieved on sloping floors, thanks to a large levelling range Certification to 3-A Sanitary Standards
Material	Stainless steel 1.4301 (AISI 304)
Supply includes	Assembly parts and seals
Load capacity	Max. 7000 N static per levelling foot
Dimensions	Thread: M12
To fit	Enclosure type: HD compact enclosure VX VX SE TS
Levelling range	122 - 175 mm
Packs of	4 pc(s).
Net weight	2 kg
Gross weight	2.342 kg
Customs tariff number	73181900
ETIM 9	EC002622
ETIM 8	EC002622
ECLASS 8.0	27189263

# Features

---

Product description

HD Levelling foot, without base mount, Stainless steel 1.4301