

# Rittal – The System.

Faster – better – everywhere.



## HD 4000.250 Levelling feet HD

State: 03/08/2025 (Source: [rittal.com/gr-en](https://www.rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# HD 4000.250 - Levelling feet HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | HD 4000.250  |
| Design                | with base attachment   |
| Benefits              | Minimises cleaning time thanks to fully covered, permanently sealed threads<br>Compensation of floor inclines up to an angle of 10° thanks to flexible base<br>Baying can even be achieved on sloping floors, thanks to a large levelling range<br>Certification to 3-A Sanitary Standards |
| Material              | Stainless steel 1.4301 (AISI 304)  |
| Supply includes       | Assembly parts and seals   |
| Load capacity         | Max. 7000 N static per levelling foot  |
| Dimensions            | Thread: M12  |
| To fit                | Enclosure type: HD compact enclosure<br>VX<br>VX SE<br>TS  |
| Levelling range       | 122 - 175 mm   |
| Packs of              | 4 pc(s).   |
| Net weight            | 2.4  |
| Gross weight          | 2.5  |
| Customs tariff number | 73181900   |
| EAN                   | 4028177707658  |
| ETIM 9                | EC002622   |
| ETIM 8                | EC002622   |

# Features

ECLASS 8.0

27189263