

# Rittal – The System.

Faster – better – everywhere.



## AS 4050.775 Wire end ferrules

State: 27/06/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4050.775 - Wire end ferrules loose

With plastic collar.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4050.775   |
| Product description      | With plastic collar.  |
| Technical specifications | Heat-resistant to 105 °C  |
| Material                 | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene  |
| Colour                   | Red   |
| Length                   | 12 mm   |
| AWG                      | 16  |
| Internal diameter        | 3.5 mm  |
| Rittal colour code       | Yes   |
| DIN colour code          | Yes   |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines.<br>For bespoke advice, please contact your Rittal sales consultant. |
| Standards                | AEH DIN 46228   |
| Delivery form            | Loose   |
| Packs of                 | 500 pc(s).  |
| Net weight               | 0.5 kg  |
| Gross weight             | 0.5 kg  |
| Customs tariff number    | 85369010  |
| ETIM 9                   | EC000005  |
| ETIM 8                   | EC000005  |
| ECLASS 8.0               | 36659290  |

# Features

---

Product description

Wire end ferrules for wire processing, 1.5 mm<sup>2</sup>, red, loose, 12 mm

# Approvals

---

Approvals

UL + C-UL (listed)

UR