

Rittal – The System.

Faster – better – everywhere.



AS 4051.582 Wire end ferrules

State: 26/06/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.582 - Wire end ferrules loose

With plastic collar.

Features

Model No.	AS 4051.582
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Yellow
Length	12 mm
AWG	18
Internal diameter	3.5 mm
Rittal colour code	Yes
Multinorm	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end ferrules for wire processing, 1.0 mm ² , yellow, loose, 12 mm

Approvals

Approvals

UL + C-UL (listed)

UR