


# Rittal – The System.

Faster – better – everywhere.



## AS 4051.604

## Wire end ferrules

State: 31/07/2025 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.604 - Wire end ferrules on a reel

With plastic collar.

## Features

Model No.	AS 4051.604
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Red
Length	10 mm
AWG	16
Internal diameter	3.5 mm
Rittal colour code	Yes
For cross-section	1.5 mm <sup>2</sup>
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	5,000 pc(s).
Net weight	5
Gross weight	0.794
Customs tariff number	85369010
EAN	4028177938656
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Approvals

---

Approvals

UL + C-UL (listed)