

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.622

## Wire end ferrules

State: 08/02/2026 (Source: [rittal.com/gr-en](http://rittal.com/gr-en))

# AS 4051.622 - Wire end ferrules loose

With plastic collar.

## Features

Model No.	AS 4051.622
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Black
Length	10 mm
AWG	16
Internal diameter	3.5 mm
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Gross weight	0.064
Customs tariff number	85369010
EAN	4028177999848
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

# Approvals

---

Approvals

UL + C-UL (listed)  
UR