

Rittal – The System.

Faster – better – everywhere.



AS 4054.002 Crimping pliers

State: 27/06/2026 (Source: rittal.com/gr-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4054.002 - Crimping pliers for wire end ferrules

Crimping tool for square or hexagonal compression, for processing wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.

Features

Model No.	AS 4054.002
Design	Straight
Product description	For use with wire end ferrules with no insulating collar to DIN 46228, Part 1 and wire end ferrules with insulating collar to DIN 46228, Part 4.
Benefits	Minimal effort required with large wire cross-sections Uniformly high quality compression Releasable ratchet Self-adjusting
Material	High-quality special tool steel
Surface finish	Matt, plated
Colour	Handle: RAL 7016 and RAL 35745
Compression	Square crimp
Direction of cable entry	Side
Dimensions	Length: 176 mm
AWG	26 - 8
For cross-section	0.14 - 10 mm ²
Packs of	1 pc(s).
Net weight	0.4 kg
Gross weight	0.449 kg
Customs tariff number	82032000
ETIM 9	EC000168
ETIM 8	EC000168

Features

ECLASS 8.0

21043811

Product description

AS crimping tool, square, for cross-section 0.14 – 10 mm²